Big Topper®

7 MEE MOVING HEAD

7 Big Bee Eyes Dyed Beam Shake

Head Lamp User Manual



Product technical parameters:

Voltage: AC90-240v

Power: 350w

Frequency: 50-60Hz

Lamp beads: 7 40W 4-in-1 lamp beads

Channel: 23CH

Control mode: DMA/master-slave/voice control

Horizontal scanning: 540 degrees Vertical scanning: 270 degrees

Strobe: 1-25 times/second or random
Display screen: LCD/English WQERFWSFRF

Net weight: 6kg

Size: 45* 26 * 40cm (cardboard box 1 inch)

23 CHANNLE MODE				
СН	FANCTION	DMX	REMARK	
1	PAN	0 - 255		
2	PAN-FINE	0 - 255		
3	TILT	0 - 255		
4	TILT-FINE	0 - 255		
5	PAN-TILT TIME	0 - 255		
6	FOCUS	0 - 255		
		0 107	Linearly moves	
		0 - 127	from 0° to 360°	
7	ROTATION	128 - 190	Rotation from fast	

191 - 192

to slow, Forward

Stop

		193 - 255	Rotation from slow
			to fast, Reverse
8	DIMMER	0 - 255	LED R,G,B,W,
			Linearly moves
			from 0-100%
9	STROBE	0 - 3	Light Off
		4 - 251	Strobe from slow
			to fast
		252 - 255	Light On
10	RED	0 - 255	Red Linearly moves
			from 0-100%
11	GREEN		Green Linearly
		0 - 255	moves from
			0-100%
12	BLUE	0 - 255	Blue Linearly
			moves from
			0-100%
13	WHITE	0 - 255	White Linearly
			moves from
			0-100%
14	RFU	0 - 255	No Uesed

n

Background Red
Linearly moves
from 0-100%
ackground Green
Linearly moves
from 0-100%
Background Blue
Linearly moves
from 0-100%
Background White
Linearly moves
from 0-100%
None
Reset
E

Routine maintenance

Cleaning and maintenance

The equipment requires daily cleaning and maintenance, and the lifespan of the equipment largely depends on the operating environment and daily cleaning and maintenance. Before opening any covers, the power should be disconnected Optical components should be lightly