





Рекомендуемые варианты размещения стеллажей в камерах POLAIR Standart

№	Камера	Модель стеллажа вариант№1 ПРОФИ	Кол-во	Модель стеллажа вариант№2 ПРОФИ-430	Кол-во
1.	КXH-2,94 (1360X1360X2200)	CM-10/5H	1	CM-10/5H-430	1
2.	КXH-4,41 (1360x1960x2200)	CM-10/5H	1	CM-10/5H-430	1
		CM-12/5H	1	CM-12/5H-430	1
3.	КXH-6,61 (1960x1960x2200)	CM-12/5H	1	CM-12/5H-430	1
		CM-15/5H	1	CM-15/5H-430	1
4.	КXH-7,71 (1960x2260x2200)	CM-15/5H	2	CM-15/5H-430	2
5.	КXH-8,81 (1960x2560x2200)	CM-15/5H	2	CM-15/5H-430	2
6.	КXH-11,75 (2560x2560x2200)	CM-10/5H	1	CM-10/5H-430	1
		CM-12/5H	2	CM-12/5H-430	2
		CM-15/5H	1	CM-15/5H-430	1
7.	КXH-11,02 (1960x3160x2200)	CM-12/5H	3	CM-12/5H-430	3
		CM-15/5H	1	CM-15/5H-430	1


Рекомендуемые схемы размещения стеллажей в камерах POLAIR Standart




KXH-2,94 (1360x1360x2200)




KXH-8,81 (1960x2560x2200)




KXH-4,41 (1360x1960x2200)




KXH-11,75 (2560x2560x2200)



KXH-6,61 (1960x1960x2200)



KXH-7,71 (1960x2260x2200)



KXH-11,02 (1960x3160x2200)